

SKINMATIC® MH Set

SKINMATIC® MH Set, metric mounting tools with shaped contact surface for SKINTOP® gland sizes up to M110x2

Info

Assembly tool for SKINTOP® gland sizes up to M110 x 2



Benefits

Fast, secure and damage-free assembly
Shaped contact surface prevents the spanner from sliding off

Application range

Special tools designed for metric SKINTOP® brass types

Product features

Assembly set manufactured from chromium-plated tool steel
The SKINMATIC® MH set consists of three special keys:
OK 16/20 mm (M12/M16)
OK 24/29 mm (M20/M25)
OK 36/45 mm (M32/M40)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002130

ETIM 5.0 Class-Description: Spanner

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002130

ETIM 6.0 Class-Description: Spanner

Note

Not subjected to RoHS directive.
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINMATIC® MH Set

Article number	Width of flat surface (mm)	Brass gland sizes	Overall length (mm)
SKINMATIC® MH-Set			
61791273	16/20, 24/29, 36/45	M 12, M 16, M 20, M 32, M 40	200 / 220 / 250
SKINMATIC® MH single wrench			
61791267	54	M 50	-
61791268	67	M 63	-
61791269	75	M 63 plus	-
61791286	95	M 75	-
61791287	115	M 90	-
61791288	135	M 110	-

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16