

EPIC® POWERLOCK Crimp contacts

Contacts, tools, accessories for circular connectors

EPIC® POWERLOCK 660A crimp contacts from 35mm² up to 240mm²

Info

Max. crimp 660 A

Do not plug with screw-type (400 A)



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® POWERLOCK Crimp contacts

Article number	Article designation	Version	Crimp sunk	PU
44420260	POWERLOCK SP M12	Contact Drain, M12 Thread for cable lugs	-	1
Source - for type A6 C				
44420261	POWERLOCK QP M12	Lamella contact source, M12 thread for cable lug	-	1
44420293	POWERLOCK SCM 35	35 mm ²	35	1
44420294	POWERLOCK SCM 50	50 mm ²	50	1
44420295	POWERLOCK SCM 70	70 mm ²	70	1
44420231	POWERLOCK SCM 95	95mm ²	95	1
44420233	POWERLOCK SCM 120	120 mm ²	120	1
44420256	POWERLOCK SCM 150	150 mm ²	150	1
44420234	POWERLOCK SCM 185	185 mm ²	185	1
44420339	POWERLOCK SCM 240 NEW	240 mm ²	240	1
44420290	POWERLOCK QCM 35	35 mm ²	35	1
44420291	POWERLOCK QCM 50	50 mm ²	50	1
44420292	POWERLOCK QCM 70	70 mm ²	70	1
44420236	POWERLOCK QCM 95	95mm ²	95	1
44420238	POWERLOCK QCM 120	120 mm ²	120	1
44420257	POWERLOCK QCM 150	150 mm ²	150	1
44420239	POWERLOCK QCM 185	185 mm ²	185	1
44420324	POWERLOCK QCM 240 NEW	240 mm ²	240	1

EPIC® POWERLOCK Crimp contacts

