

EPIC® MC 2.5 stamped contacts

For inserts and modules of the EPIC® rectangular connectors

The pressed contacts for conductor cross-section from 0.5 to 2.5 mm² are available as female and male pins.

Info

silver plated and passivated contacts

Two crimp areas with wire and insulation crimp



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC 2.5 stamped contacts

Article number	Article description	Contact type	Conductor cross-section (mm ²)	Surface	Stripping length (mm)	Pieces / PU
Contacts						
11201000	MC 2.5 stamped	male	0.5 - 1.5	Ag	3.5 + 0.5	100
11205000	MC 2.5 stamped	female	0.5 - 1.5	Ag	3.5 + 0.5	100
11202000	MC 2.5 stamped	male	1.5 - 2.5	Ag	3.5 + 0.5	100
11206000	MC 2.5 stamped	female	1.5 - 2.5	Ag	3.5 + 0.5	100