

EPIC® ULTRA H-B 24 AG QB

The robust and reliable industry connector housing as EMC version



EPIC® Rectangular connector housing EMC protection, corrosion resistant, UL50E, Nema250

Info

EMC protection

Corrosion-resistant

Made in Germany



Good chemical resistance



Wide clamping range



Assembly time



Optimum strain relief



Space requirement



Robust



Integrated SKINTOP[®] cable gland



Connector with standard housing unit

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® ULTRA H-B 24 AG QB



Interference signals



Waterproof

Benefits

Optimum, low-resistance 360° screening

All-purpose due to high corrosion resistance and high environmental protection.

Space-saving due to compact dimensions.

Faster than any other comparable system

High mechanical resistance

Application range

In EMC-sensitive environments

For fixed and flexible applications (e.g. machinery building, wind turbines)

Construction machinery

Electric motor manufacturing

Product features

Housings with the BRUSH addition come with BRUSH cable screen contacting

Pluggable with standard housings

Corrosion-resistant according to DIN EN 6988

Resistance to cyclic salt spray is tested according to IEC 68-2-52, severity level 2

Salt spray testing according to DIN EN ISO 9227, method NSS, period of test 480 hours

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: nickel-plated zinc die-casting

Lever and bolts: stainless steel

Sealing: NBR

Cable gland

Body: nickel-plated brass

Insert: PA

Seal: special elastomer

Protection rating:

IP 65

NEMA 250, UL50E: 12 (latched)

Temperature range:

-40°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® ULTRA H-B 24 AG QB

Article number	Article description	Pieces / PU
H-B housing: panel-mount base (double lever)		
70250222	ULTRA H-B 24 AG QB	1