


## FLEXIMARK® Label LMB

LMB labels can be used in different marking collars (up to 30 mm). Together with our label software, you can easily print LMB labels with a laser printer, both sides of the label can be printed.

### Info

Included in FLEXIMARK® sample bag (article no. M3251010)



Good chemical resistance



Halogen-free



UV-resistant

### Benefits

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Printable on both sides

### Application range

Suitable labels for snap-on collars, closed collars and collars for cable ties (see section "Character holders and accessories")

### Note

Can be printed with the FLEXIMARK® Software and a commercial laser printer

Insert sheet in manual paper feed compartment

Optimum printing results from laser printers are achieved with straight sheet feed-in

### Included

Perforated DIN A5 sheets

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001288

ETIM 6.0 Class-Description: Labelling material

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Label LMB

On request:	Also available as rolls for thermal transfer printers (TMB)
Colour delivered:	Yellow/White (can be printed on both sides)
Material:	Halogen-free polyester Thickness: 0.175 mm
Temperature range:	-40 °C to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

**FLEXIMARK® Label LMB**

Article number	Article designation	Colour	Width x length (mm)	Markers / PU	PU
83254680	FLEXIMARK® Label LMB 30-4.6 YEWH	yellow/white	4.6 x 30.0	480	1