

SILVYN® LTPG-M

SILVYN® LTPG-M is a nickel-plated brass conduit fitting that offers an protection degree up to IP66/67/68/69



Corrosion-resistant



Maximum vibration protection



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust

Benefits

High tensile strength

Vibration protection

High sealing performance

Application range

In combination with protective conduit:

SILVYN® LTP

Applications with high mechanical stress

Used in areas where liquids are present

Product Make-up

Metric connection thread

Hexagonal collar

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LTPG-M

Threaded sleeve
Cap nut

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Certifications:	IEC EN 61386-23
Material:	Body: nickel-plated brass Seal: PA compression seal
Protection rating:	IP66 IP67 IP68 (5 bar) IP69
Temperature range:	-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LTPG-M

Article number	Metric size	SW wrench size mm	Thread length mm	Suitable for SILVYN® LTP	Pieces / PU
SILVYN® LTPG-M					
55510200	12 x 1.5	20.0	10	10	10
55510210	16 x 1.5/1	20.0	10	12	10
55510220	16 x 1.5/2	24.0	10	16	10
55510230	20 x 1.5/1	24.0	12	16	10
55510240	20 x 1.5/2	26.0	12	20	10
55510250	25 x 1.5	33.0	14	25	10
55510260	32 x 1.5	40.0	15	32	2
55510270	40 x 1.5	50.0	16	40	1
55510280	50 x 1.5	58.0	16	50	1
55510290	63 x 1.5	70.0	20	63	1