

SILVYN® KCLICK GPZ-M

SILVYN® KCLICK GPZ-M - metric conduit fitting with integrated cable strain relief for SILVYN® RILL



Wide clamping range



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

Benefits

- Fast assembly
- Easy to disassemble
- Additional cable strain relief
- Additional cable sealing

Application range

In combination with protective conduit:

SILVYN® RILL PA 6

SILVYN® RILL PA 12

Robot-building

Used in areas where cables and wires need to be provided with strain relief and additional sealing

Norm references / Approvals

UL FILENUMBER E308201

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KCLICK GPZ-M

Product Make-up

Metric connection thread
Cable gland
Body with inner sealing
Upper part with snap-in sleeve

Note

PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® KLICK GPZ-M

Article number	Metric size	Clamping range in mm	SW wrench size mm	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK, GPZ-M grey								
55500800	12 x 1.5	4 - 6.5	16	8	6.5	10	10	20
55500810	16 x 1.5	5 - 9.5	18	8	9.5	13	13	20
55500820	20 x 1.5	8 - 12	24	8	13	15.8	16	20
55500830	25 x 1.5	11 - 16	27	8	16	21.2	21	10
55500840	32 x 1.5	15 - 21	34	10	18	28.5	28	10
55500850	40 x 1.5	16 - 26	40	10	25	34.5	34	10
55500860	50 x 1.5	27 - 35	55	12	32	42.5	42	10
55500870	63 x 1.5	32 - 42	65	12	44	54.5	54	10
SILVYN® KLICK, GPZ-M black								
55500805	12 x 1.5	4 - 6.5	16	8	6.5	10	10	20
55500815	16 x 1.5	5 - 9.5	18	8	9.5	13	13	20
55500825	20 x 1.5	8 - 12	24	8	13	15.8	16	20
55500835	25 x 1.5	11 - 16	27	8	16	21.2	21	10
55500845	32 x 1.5	15 - 21	34	10	18	28.5	28	10
55500855	40 x 1.5	16 - 26	40	10	25	34.5	34	10
55500865	50 x 1.5	27 - 35	55	12	32	42.5	42	10
55500875	63 x 1.5	32 - 42	65	12	44	54.5	54	10