


SILVYN® US FPS-EDU

SILVYN® US is a PG threaded nickel-plated brass conduit fitting that offers IP40 / IP54 / IP66 protection degree depending on the used conduit



Maximum vibration protection



Space requirement



Robust



Temperature-resistant

Benefits

- High tensile strength
- Space-saving
- Vibration protection
- All-purpose
- Fast and easy assembly

Application range

In combination with protective conduit:
SILVYN® FPS-EDU
Mechanical engineering
Plant engineering

Product features

Compact design

Product Make-up

- PG connection thread
- Hexagonal collar
- Threaded sleeve
- Sealing element
- Cap nut

Last Update (15.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® US FPS-EDU

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Body: nickel-plated brass Sealing ring: TPE
Protection rating:	IP 54 (with SILVYN® FPS-EDU)
Temperature range:	-40°C to +125°C

Note

Other variations with multiple SKINTOP® DIX-M sealing inserts are available upon request.
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® US FPS-EDU

Article number	PG size	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® US for SILVYN® FPS-EDU				
55502689	9	8.5	14	50
55502690	11	11	17	50
55502692	16	14.5	21	50
55502693	21	19.5	27	25
55502694	29	27.5	36	25
55502696	36	35.5	45	20
55502697	48	47	56	10