

SILVYN® FG NM

SILVYN® FG NM with blue jacket for certified use in the food and beverage industry

Info

All-plastic conduit

Specifically for the food and drinks industry



Food & Beverage



Good chemical resistance



Reliability



Waterproof

Benefits

FDA-approved outer sheath

Smooth, blue surface makes it easy to clean

Protects against liquids

Application range

Food and beverage industry, especially for production and processing equipment of milk and meat products

Food packaging machinery

Pharmaceutical industry

Mechanical engineering

Plant engineering

Product features

Flexible

Dimensionally stable

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FG NM

Flame-retardant

Norm references / Approvals

Certified according to FDA CFR 21 and NSF 51 (standard for the USA)

ECOLAB®

Industry standard in the field of professional cleaning and disinfection in the food and beverage industry

Product Make-up

Hard PVC inner spiral

Special, FDA-approved plastic sheath

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001177 ETIM 5.0 Class-Description: Protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001177 ETIM 6.0 Class-Description: Protective plastic hose
Certifications:	FDA CFR 21 NSF 51
On request:	Also in grey and white colour
Colour delivered:	Blue
Material:	Special soft PVC sheath with hard PVC spiral
Temperature range:	-20 °C to +60 °C Short-term: +80 °C

Note

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FG NM

Article number	Nominal size	ID x OD mm	Bending radius (mm)	PU ring (m)
SILVYN® FG NM blue				
55503370	3/8"	12.6 x 17.8	70	30
55503371	1/2"	16.0 x 21.1	100	30
55503372	3/4"	21.0 x 26.4	130	30
55503373	1"	26.5 x 33.1	180	30
55503374	1 1/4"	35.1 x 41.8	225	15
55503375	1 1/2"	40.3 x 47.8	255	15
55503376	2"	51.6 x 59.9	310	15