

DSA 0110 + DSA 0725 crimping pliers

DSA 0110 and DAS 0725: Crimping pliers for pressing insulated connectors as insulated cable lugs and blade/panel connectors from 0,1 to 1,5 mm² and 0,5-2,5 mm²



Reliability

Benefits

- Suitable for left and right-handed users
- Less force required for perfect pressing
- Clearly marked press moulds
- Cross-section of press matrix is embossed in the cable lugs for checking
- Pressing according to the forced finish system

Application range

- Safety pressing pliers for insulated connections
- For insulated cable lugs, blade connectors and other connectors

Product features

- Emergency release, if the pressing operation needs to be interrupted

Norm references / Approvals

- Tested in accordance with DIN standards

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

General:

Adjustable crimping pressure

Note:

Crimping profile: Oval

Note

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

DSA 0110 + DSA 0725 crimping pliers

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

DSA 0110 + DSA 0725 crimping pliers

Article number	Article designation	For mm ²	Weight (kg)	Length (mm)	Pieces / PU
61722050	DSA 0110	0.1 - 1.5	0.35	225	1
61722060	DSA 0725	0.5 - 2.5	0.35	192	1