

KNIPEX Cable shear

KNIPEX cable shears for conductors with an outer diameter of up to 20 mm, ergonomic design means it is particularly easy to use, manufactured in Germany

Info

Less power required due to favourable transmission ratio and new blade geometry



Benefits

Special two-blade structure divides the cutting process into pre-cut and post-cut

Easy and clean cut by using only one hand

High ergonomics thanks to multi-component handles

Insulated handles allow working under voltage up to 1000V

Application range

Cuts copper and aluminium cables

Product features

Precision ground, hardened blades

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

High-grade special tool steel, forged, chrome plated

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX Cable shear

Article number	Article designation	Cable diameter mm	Weight (kg)	Length (mm)
62120523	Cable shear KASI 20	20	0.34	200