


Ty-Fast® Cable ties

The TY - FAST® cable tie made of PA 6.6 is the standard cable tie for many applications. It is fulfilling several approvals.



Halogen-free



UV-resistant

Benefits

The integrally formed polyamide pawl combines low insertion and high locking strength. Sure grip tab keeps the tail from popping out while being threaded, then holds it securely for final tightening by hand or tool.

Application range

Multipurpose cable tie for many applications

Norm references / Approvals

File number: E49405, see table

Fire behaviour according to UL94 V-2

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000046

ETIM 5.0 Class-Description: Cable tie

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000046

ETIM 6.0 Class-Description: Cable tie

Material:

Polyamide 6.6

Halogen-free and silicone-free

Temperature range:

-40 °C to +85 °C

Note

Last Update (10.09.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Ty-Fast® Cable ties

TY-FAST® is a registered trademark of ABB.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Ty-Fast® Cable ties

Article number	Article description	UL certification	Length x width (mm)	Bundling Ø (mm)	Tensile strength (N)	Pieces / PU
Natural						
61810350	TY100-18	yes	112.0 x 2.4	25	80	1000
61810360	TY125-18	yes	136.0 x 2.4	32	80	1000
61810380	TY125-40	yes	141.0 x 3.6	32	180	1000
61810390	TY200-40	yes	205.0 x 3.6	50	180	1000
61810400	TY300-40	yes	290.0 x 3.6	76	180	1000
61810410	TY175-50	yes	186.0 x 4.6	44	220	1000
61810420	TY300-50	yes	291.0 x 4.6	76	220	1000
61810430	TY400-50	yes	366.0 x 4.6	102	220	1000
61810440	TY200-120	yes	219.0 x 7.6	50	540	500
61810450	TY400-120	yes	375.0 x 7.6	102	540	500
Black (UV-resistant)						
61810460	TY100-18x	yes	112.0 x 2.4	25	80	1000
61810470	TY125-18x	yes	136.0 x 2.4	32	80	1000
61810490	TY125-40x	yes	141.0 x 3.6	32	180	1000
61810500	TY200-40x	yes	205.0 x 3.6	50	180	1000
61810510	TY300-40x	yes	290.0 x 3.6	76	180	1000
61810520	TY175-50x	yes	186.0 x 4.6	44	220	1000
61810530	TY300-50x	yes	291.0 x 4.6	76	220	1000
61810540	TY400-50x	yes	366.0 x 4.6	102	220	1000
61810550	TY200-120x	yes	219.0 x 7.6	50	540	500
61810560	TY400-120x	yes	375.0 x 7.6	102	540	500

Last Update (10.09.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16