

UNITRONIC® LiYCY (TP)

Screened data transmission cable with colour code acc. to DIN 47100 and twisted pairs

UNITRONIC® LiYCY (TP): Low-frequency PVC data cable, DIN 47100 coded, 0.34² Maxi TERMI-POINT®, Twisted pairs, Flame retardant, Screened, Instrumentation Control

Info

TP = twisted pair

Further dimensions/colours on request

CPR: Article number choice under www.lappkabel.com/cpr



Interference signals

Benefits

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)

Overall braid minimises electrical interference

Application range

Can be used multifunctional in electronics of computer systems, electronic control equipment, office machines, balances, etc.
Dry or damp rooms

Product features

Good protection against capacitive interference from electric fields (e.g. power cable)

Flame-retardant according IEC 60332-1-2

Norm references / Approvals

Based on VDE 0812

Product Make-up

Last Update (04.09.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® LiYCY (TP)

Fine-wire strand made of bare copper wires
Core insulation made of PVC
TP structure
Tinned-copper braiding
Outer sheath made of PVC
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	C/C: approx. 120 nF/km C/S: approx. 160 nF/km
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Fine copper wire strands
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 6 x outer diameter
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® LIYCY (TP)

Article number	Dimension and cross section in mm ²	Outer diameter [mm]	Copper index [kg/km]	Weight [kg/km]
UNITRONIC® LIYCY (TP)				
0035131	2 x 2 x 0.14	5.3	18.5	39
0035141	3 x 2 x 0.14	5.8	23	48
0035132	4 x 2 x 0.14	6.2	26.6	54
0035133	6 x 2 x 0.14	7.1	48.5	85
0035150	8 x 2 x 0.14	8.2	53.7	97
0035134	10 x 2 x 0.14	8.7	59	110
0035135	12 x 2 x 0.14	8.9	66	142
0035136	16 x 2 x 0.14	10.2	79	154
0035142	20 x 2 x 0.14	11.3	97	184
0035137	25 x 2 x 0.14	12.5	113	238
0035800	2 x 2 x 0.25	6.3	28	54
0035801	3 x 2 x 0.25	7.1	39.6	68.5
0035802	4 x 2 x 0.25	7.6	44.9	81
0035803	6 x 2 x 0.25	8.5	69.5	115
0035804	8 x 2 x 0.25	10.3	76.9	130
0035805	10 x 2 x 0.25	11	102	158
0035806	12 x 2 x 0.25	11.3	120	190
0035807	16 x 2 x 0.25	12.5	146.5	238
0035808	25 x 2 x 0.25	16.1	205	344
0035810	2 x 2 x 0.5	7.9	48.1	93
0035811	3 x 2 x 0.5	8.7	73.7	116
0035812	4 x 2 x 0.5	9.4	82	127
0035813	6 x 2 x 0.5	11.1	110	198
0035814	8 x 2 x 0.5	13.1	139	259
0035816	12 x 2 x 0.5	14.9	198.3	354
0035817	16 x 2 x 0.5	16.5	240	459
0035820	2 x 2 x 0.75	8.5	58	106
0035821	3 x 2 x 0.75	9.4	84	140
0035822	4 x 2 x 0.75	10.7	108	179
0035827	5 x 2 x 0.75	11.1	126	215
0035823	6 x 2 x 0.75	12.1	146	246
0035824	8 x 2 x 0.75	14.7	180	305
0035825	12 x 2 x 0.75	16.2	261	456

UNITRONIC® LIYCY (TP)

Article number	Dimension and cross section in mm ²	Outer diameter [mm]	Copper index [kg/km]	Weight [kg/km]
0035830	2 x 2 x 1.0	9	84	142
0035831	3 x 2 x 1.0	10	96	173
0035832	4 x 2 x 1.0	11.3	121	212
0035836	5 x 2 x 1.0	11.8	161	266

Last Update (04.09.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16