

EPIC® H-A 4

H-A inserts with screw termination up to 2.5 mm² wire cross section

The robust insert has a screw connection that is easy to operate and can be used, for example, in control systems.

Info

Insert for three-phase current application with neutral conductor

Easy to assemble due to straight conductor entry

Made in Germany



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy



Assembly time



Space requirement



Variety of approval certifications

Benefits

The small H-A 3 / H-A 4 are used whenever there is minimal space.

Easy to service screw connection

Easy cable connection with straight cable entry in the contacts

Application range

Machine and equipment manufacturing

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 4

Control engineering
Apparatus construction
Vehicle construction

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 Class-Description: Contact insert for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors
Rated voltage (V):	IEC: 400 V UL: 600 V CSA: 600 V
Rated impulse voltage:	4 kV
Rated current (A):	IEC: 23 A UL: 10 A CSA: 10 A
Pollution degree:	3
Flammability:	UL94 V-0
Contact resistance:	1.5 - 4 mohm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	4 + PE
Termination methods:	Screw termination: 0.5 - 2.5 mm ² (2.5 mm ² with conductor end sleeves depending on the crimping profile)
Stripping length (mm):	6
Cycle of mechanical operation:	100
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® H-A 4

Article number	Article description	Contact type	Number of operating contacts	Packaging unit
H-A 4 screw termination				
10431000	EPIC® H-A 4 SS	male	1 - 4	10
10432000	EPIC® H-A 4 BS	female	1 - 4	10

EPIC® H-A 4

