

EPIC® POWER LS1.5 Contacts male

Contacts, tools, accessories for circular connectors

EPIC® POWER LS1.5 Contacts male for size 1.5 circular connector series

Info

All contacts are high quality gold plated

Only available as crimp version due to the high mechanical stress in servo applications

Made in Germany



Good chemical resistance



Corrosion-resistant



Mechanical resistance



Optimum strain relief



Robust



Reliability

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (26.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWER LS1.5 Contacts male

Article number	Article designation	Version	For design	Pieces / PU
44429335	LS1.5 A SCEM 3,6MM AU 1,0-2,5	3.6 mm male 1.0 - 2.5 mm ²	for type A1, A3	10
44429337	LS1.5 A SCEM 3,6MM AU 4,0-6,0	3.6 mm male 4.0 - 6.0 mm ²	for type A1, A3	10
44429338	LS1.5 A SCEM 3,6MM AU 6,0-10,0	3.6 mm male 6.0 - 10.0 mm ²	for type A1, A3	10
44429326	LS1.5 F SCEM 3,6MM AU 1,0-2,5	3.6 mm male 1.0 - 2.5 mm ²	for type F6	10
44429327	LS1.5 F SCEM 3,6MM AU 2,5-4,0	3.6 mm male 2.5 - 4.0 mm ²	for type F6	10
44429328	LS1.5 F SCEM 3,6MM AU 4,0-6,0	3.6 mm male 4.0 - 6.0 mm ²	for type F6	10
44429329	LS1.5 F SCEM 3,6MM AU 6,0-10,0	3.6 mm male 6.0 - 10.0 mm ²	for type F6	10
44429340	LS1.5 A SCEM 2MM AU 0,25-1,0	2 mm male 0.25 - 1.0 mm ²	for type A1, A3	10
44429341	LS1.5 A SCEM 2MM AU 0,75-1,5	2 mm male 0.75 - 1.5 mm ²	for type A1, A3	10
44429330	LS1.5 F SCEM 2MM AU 0,25-1,0	2 mm male 0.25 - 1.0 mm ²	for type F6	10
44429331	LS1.5 F SCEM 2MM AU 0,75-1,5	2 mm male 0.75 - 1.5 mm ²	for type F6	10
44429332	LS1.5 F SCEM 2MM AU 1,0-2,5	2 mm male 1.0 - 2.5 mm ²	for type F6	10
44429333	LS1.5 F SCEM 2MM AU 2,5-4,0	2 mm male 2.5-4.0 mm ²	for type F6	10

Last Update (26.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

EPIC® POWER LS1.5 Contacts male

