

SKINDICHT® O-ring FKM metric

SKINDICHT® O-ring FKM metric, sealing ring, to protect against oils, acids, chemicals at parts under extreme conditions



Good chemical resistance



Acid-resistant



Temperature-resistant

Application range

For sealing the housing reliably to protect against oils, acids, and chemicals at the connection thread of a gland or other similar parts under extreme conditions

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring
Colour delivered:	Green
Material:	FKM
Temperature range:	-20 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® O-ring FKM metric

Article number	Article designation / size	Inner Ø (mm)	Cable thickness (mm)	Pieces / PU
52122001	M 12 x 1,5	9.0	1.5	100
SKINDICHT® O-ring FKM metric				
52122000	M 12 x 2,0	9.0	2	100
52122010	M 16 x 2,0	13.0	2	100
52122021	M 20 x 1,5	17.0	1.5	100
52122020	M 20 x 2,0	17.0	2	100
52122030	M 25 x 2,0	22.0	2	100
52122040	M 32 x 2,0	28.0	2	50
52122050	M 40 x 2,0	36.0	2	50
52122060	M 50 x 2,0	46.0	2	25
52122070	M 63 x 2,0	57.0	2	25

Last Update (27.03.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16