

SKINTOP® DV

SKINTOP® DV, PG multiple sealing inserts, prevents humidity from seeping in, as protection of unused connection points



Benefits

Prevents humidity from seeping into the housing

Application range

These seals are placed into the sealing ring of the SKINTOP® cable glands Preparations $\begin{tabular}{ll} \hline \end{tabular} \label{table_equations}$

Protection of unused connection points

Note

When assembled professionally and properly, the protection class of IP 68 can be reached Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5: ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6: ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Colour delivered: Black Material: CR

Temperature range: -30°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (28.03.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SKINTOP® DV

Article designation / size Clamping range Ø F mm Height (mm) Pieces / PU Article number SKINTOP® DV DV 7 7.0 6.5 500 53800640 DV 9 8.5 7.5 500 53800641 8.5 53800579 DV 11 10.5 250 DV 13,5 12.5 8.5 250 53800583 DV 16 14.5 9.0 250 53800642 DV 21 18.5 11.0 100 53800643