

## SKINTOP® DV

SKINTOP® DV, PG multiple sealing inserts, prevents humidity from seeping in, as protection of unused connection points



Assembly time



Reliability

### Benefits

Prevents humidity from seeping into the housing

### Application range

These seals are placed into the sealing ring of the SKINTOP® cable glands

Preparations

Protection of unused connection points

### Note

When assembled professionally and properly, the protection class of IP 68 can be reached

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Colour delivered:

Black

Material:

CR

Temperature range:

-30°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® DV**

Article number	Article designation / size	Clamping range Ø F mm	Height (mm)	Pieces / PU
SKINTOP® DV				
53800640	DV 7	7.0	6.5	500
53800641	DV 9	8.5	7.5	500
53800579	DV 11	10.5	8.5	250
53800583	DV 13,5	12.5	8.5	250
53800642	DV 16	14.5	9.0	250
53800643	DV 21	18.5	11.0	100

Last Update (27.03.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16