

SILVYN® KLICK-M

SILVYN® KLICK-M - metric conduit fitting for SILVYN® RILL



Assembly time



Temperature-resistant



Variety of approval certifications

Benefits

- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance
- Can be rotated

Application range

In combination with protective conduit:
SILVYN® RILL PA 6
SILVYN® RILL PA 12
Robot-building
Rotating applications

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

- Metric connection thread
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KLICK-M

Note

PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® KLICK-M

Article number	Metric size	SW wrench size mm	Overall length mm	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK-M grey								
55501000	10 x 1.0	16	34.5	12	6	10	10	50
55501010	12 x 1.5	18	37	12	7	13	13	50
55501020	16 x 1.5/1	18	37	12	10	13	13	50
55501030	16 x 1.5/2	21	39	12	11	15.8	16	50
55501040	20 x 1.5/1	21	39	13	12	15.8	16	50
55501050	20 x 1.5/2	27	44.5	13	16	21.2	21	50
55501060	25 x 1.5	34	47	13	20.5	28.5	28	25
55501070	32 x 1.5	40	51	15	25.5	34.5	34	25
55501080	40 x 1.5	55	76	17	32	42.5	42	25
55501090	50 x 1.5	65	88	17	42.5	54.5	54	10
55500990	63 x 1.5	70	88	17	49	54.5	54	10
SILVYN® KLICK-M black								
55501005	10 x 1.0	16	34.5	12	6	10	10	50
55501015	12 x 1.5	18	37	12	7	13	13	50
55501025	16 x 1.5/1	18	37	12	10	13	13	50
55501035	16 x 1.5/2	21	39	12	11	15.8	16	50
55501045	20 x 1.5/1	21	39	13	12	15.8	16	50
55501055	20 x 1.5/2	27	44.5	13	16	21.2	21	50
55501065	25 x 1.5	34	47	13	20.5	28.5	28	25
55501075	32 x 1.5	40	51	15	25.5	34.5	34	25
55501085	40 x 1.5	55	76	17	32	42.5	42	25
55501095	50 x 1.5	65	88	17	42.5	54.5	54	10
55500995	63 x 1.5	70	88	17	49	54.5	54	10

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16