SILVYN® MSK-M BRUSH

SILVYN® MSK-M BRUSH - nickel-plated brass conduit fitting with EMC screening, interated cable strain relief

Info
Conduit gland with the innovative BRUSH solution
Optimum 360° screen contact





- Wide clamping range
- Maximum vibration protection
- Mechanical resistance
- Assembly time
- Optimum strain relief
- Robust
- Reliability
- Integrated SKINTOP® cable gland
- Interference signals

Benefits
Easy installation

Last Update (18.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® MSK-M BRUSH

Faster, easier screen contact
Optimum cable and conduit strain relief
Maximum cable sealing
Wide clamping range

Application range

Mechanical engineering
Plant engineering
Heavy industry
In EMC-sensitive environments

Product features

Combination of SILVYN® and SKINTOP®

Note

For suitable accessories, refer to SKINTOP® metric accessories

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Basis type: Body: nickel-plated brass Conduit connector seal: CR/NBR Tube seal: TPE EMC brush: brass
Protection rating:	Cable: IP 68 Conduit: IP 40 with SILVYN® AS, EDU-AS, EMC AS-CU IP 65 with SILVYN® AS-P
Temperature range:	-30 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2025 Lapp Group - Technical changes reserved

LAPP

SILVYN® MSK-M BRUSH

PRODUCT INFORMATION

Article number	Metric size	Clamping range in mm	Clear opening (mm)	Suitable for conduit OØ (mm)	Pieces / PU
SILVYN® MSK-M BRUSH for SILVYN® AS					
55506020	25 x 1.5	9.0 - 17.0	14.5	21	10
55506021	32 x 1.5	11.0 - 21.0	19.5	27	1
55506022	40 x 1.5	19.0 - 28.0	26.5	36	1
55506023	50 x 1.5	27.0 - 35.0	36	45	1
55506024	63 x 1.5	34.0 - 45.0	45.5	56	1
SILVYN® MSK-M BRUSH for SILVYN® AS-P / EDU-AS / EMC AS-CU					
55506025	25 x 1.5	9.0 - 17.0	14.5	21	10
55506026	32 x 1.5	11.0 - 21.0	19.5	27	1
55506027	40 x 1.5	19.0 - 28.0	26.5	36	1
55506028	50 x 1.5	27.0 - 35.0	36	45	1
55506029	63 x 1.5	34.0 - 45.0	45.5	56	1

Last Update (18.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16