

## SILVYN® MSK-M BRUSH

SILVYN® MSK-M BRUSH - nickel-plated brass conduit fitting with EMC screening, integrated cable strain relief

### Info

Conduit gland with the innovative BRUSH solution  
Optimum 360° screen contact



Wide clamping range



Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief



Robust



Reliability



Integrated SKINTOP<sup>®</sup> cable gland



Interference signals

### Benefits

Last Update (01.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® MSK-M BRUSH

Easy installation  
Faster, easier screen contact  
Optimum cable and conduit strain relief  
Maximum cable sealing  
Wide clamping range

### Application range

Mechanical engineering  
Plant engineering  
Heavy industry  
In EMC-sensitive environments

### Product features

Combination of SILVYN® and SKINTOP®

### Note

For suitable accessories, refer to SKINTOP® metric accessories

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Basis type: Body: nickel-plated brass Conduit connector seal: CR/NBR Tube seal: TPE EMC brush: brass
Protection rating:	Cable: IP 68 Conduit: IP 40 with SILVYN® AS, EDU-AS, EMC AS-CU IP 65 with SILVYN® AS-P
Temperature range:	-30 °C to +100 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® MSK-M BRUSH**

Article number	Metric size	Clamping range in mm	Clear opening (mm)	Suitable for conduit Ø (mm)	Pieces / PU
SILVYN® MSK-M BRUSH for SILVYN® AS					
55506020	25 x 1.5	9.0 - 17.0	14.5	21	10
55506021	32 x 1.5	11.0 - 21.0	19.5	27	1
55506022	40 x 1.5	19.0 - 28.0	26.5	36	1
55506023	50 x 1.5	27.0 - 35.0	36	45	1
55506024	63 x 1.5	34.0 - 45.0	45.5	56	1
SILVYN® MSK-M BRUSH for SILVYN® AS-P / EDU-AS / EMC AS-CU					
55506025	25 x 1.5	9.0 - 17.0	14.5	21	10
55506026	32 x 1.5	11.0 - 21.0	19.5	27	1
55506027	40 x 1.5	19.0 - 28.0	26.5	36	1
55506028	50 x 1.5	27.0 - 35.0	36	45	1
55506029	63 x 1.5	34.0 - 45.0	45.5	56	1

Last Update (01.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16