Valid from: DATA SHEET


EPIC® MHB 6 MULTI-FRAME



Description

30.01.2020

- Multi- frame for recording own and third-party modules
- EPIC® MH system is pluggable with the market standard
- The mixing of various functions in one connector ensures a high degree of flexibility
- PE Connection from 1mm² to 6mm² with wire end ferrule, 10mm² with adapter
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3



General Characteristics

Product description EPIC MHB 6 R (a, b)
Series MH Multi-frame
Version Female

Number of Modules 2

Surfaces

Frame Zinc die casting alloy

Standard

Safety Standard IEC 61984

44423235


DATA SHEET


Valid from: 30.01.2020

EPIC® MHB 6 MULTI-FRAME



Technical Drawing







Automation



Industrial machinery and plant engineering



Wind Energy

Info

Frame system for modules

Various functions can be used together in one connector

Product features

The MCR "male" frame version is designed for use with modules with male contacts; the "female" version is designed for use with modules with female contacts. The high design is to be used for sleeve housings

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: ERTC1/PDP	Document: DB44423235EN	Page 2 of 2
Released: IVSE1/PDP	Version: 02	