

SKINDICHT® HYGIENIC BL-M






SKINDICHT® HYGIENIC BL-M, stainless steel blind plugs with hygienic design for closing pre-threaded holes

Info

Ideal for hygienic critical areas - resistant, edge-free, robust and reliable

No gaps, voids or outer lying thread - so no risk of contamination of food machines, facilities or components



-  Food & Beverage
-  Good chemical resistance
-  Corrosion-resistant
-  Oil-resistant
-  Robust
-  Reliability
-  Temperature-resistant
-  UV-resistant

Benefits

For closing pre-threaded holes

Assembling with a wrench

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® HYGIENIC BL-M

Application range

Food machinery, equipment and components

For use in **product zone**

Pharmaceutical industry

Norm references / Approvals

NSF/ANSI 169

Hygienic design for machinery and components

ECOLAB®

Industry standard in the field of professional cleaning and disinfection in the food and beverage industry

FDA 21 CFR 177.2600

Special sealing element for food and beverage industry in North America

DIN EN 1672-2

Guideline for the design of machinery

DIN EN ISO 14159

Security of machinery – Hygienic requirements for the design of machinery

Product Make-up

Material and shape provide an easy and safe cleaning

By the blue coloring of the sealing material clearly distinguishable from foodstuffs

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Material:

Body: stainless steel - V4A (1.4404 / 316L)

Sealing: special elastomer (FKM)

Protection rating:

IP 68 - 10 bar

Temperature range:

-20°C to +220°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® HYGIENIC BL-M

Article number	Article designation / size	SW wrench size mm	Overall length C mm	Thread length D mm	Outer Ø (mm)	Pieces / PU
52103490	M 12 x 1,5	16	16.9	6.5	18.8	5
52103491	M 16 x 1,5	20	17.9	7	22.8	5
52103492	M 20 x 1,5	24	19.9	8	26.8	5
52103493	M 25 x 1,5	29	20.7	8	31.8	5
52103488	M 32 x 1,5	36	22.5	9	39.6	5
52103489	M 40 x 1,5	45	23.5	9	49.0	5