

## SKINDICHT® DTN

SKINDICHT® DTN, duct, can be used as multiple-duct sleeve, with strain relief, for cables from 4-32mm cable diameter



Optimum strain relief

### Benefits

Can be used as multiple-duct sleeve  
Strain relief

### Application range

Grommets for cables from 4 to 32 mm cable diameter.

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000879 ETIM 5.0 Class-Description: Feed through spout
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000879 ETIM 6.0 Class-Description: Feed through spout
Colour delivered:	Black
Material:	CR
Temperature range:	-30°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® DTN**

Article number	Article designation / size	Ø F mm	Metal thickness (mm)	Hole in housing Ø (mm)	Sleeve inner Ø (mm)	Pieces / PU
SKINDICHT® DTN						
52105020	DTN 1	4.0 - 9.0	2.5	16	9	50
52105030	DTN 2	7.0 - 12.0	2.5	19	12	50
52105040	DTN 3	12.0 - 17.5	2.5	25	18	50
52105050	DTN 4	18.0 - 23.0	2.5	32	25	25
52105060	DTN 5	25.0 - 29.0	3.0	38	32	25

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16