

SKINDICHT® MR-M

SKINDICHT® MR-M, reducer, enables the use of cable gland with smaller connection threads than the existing threaded holes



Space requirement



Reliability



Connector with standard housing unit

Benefits

Corrects the size difference between the connection thread of a cable gland and the threaded hole in an enclosure.

Provides flexibility in the selection of a cable gland, as the selection is independent to the threaded hole of the enclosure.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Application range

For use with a metric cable gland whose connection thread is smaller than the existing threaded hole.

Withstands high chemical and mechanical stress.

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

On request:

Also available with pre-installed O-ring

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® MR-M

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® MR-M

Article number	Thread, male M1	Thread, female M2	Pieces / PU
SKINDICHT® MR-M			
52104310	16 x 1.5	12 x 1.5	100
52104311	20 x 1.5	12 x 1.5	100
52104312	20 x 1.5	16 x 1.5	100
52104313	25 x 1.5	16 x 1.5	50
52104314	25 x 1.5	20 x 1.5	50
52104315	32 x 1.5	20 x 1.5	50
52104316	32 x 1.5	25 x 1.5	50
52104317	40 x 1.5	25 x 1.5	25
52104318	40 x 1.5	32 x 1.5	25
52104319	50 x 1.5	32 x 1.5	25
52104320	50 x 1.5	40 x 1.5	10
52104321	63 x 1.5	40 x 1.5	10
52104322	63 x 1.5	50 x 1.5	10
52006575	72 x 2	63 x 1.5	1
52104310LF	16 x 1.5	12 x 1.5	100
52104311LF	20 x 1.5	12 x 1.5	100
52104312LF	20 x 1.5	16 x 1.5	100
52104313LF	25 x 1.5	16 x 1.5	50
52104314LF	25 x 1.5	20 x 1.5	50
52104315LF	32 x 1.5	20 x 1.5	50
52104316LF	32 x 1.5	25 x 1.5	50
52104317LF	40 x 1.5	25 x 1.5	25
52104318LF	40 x 1.5	32 x 1.5	25
52104319LF	50 x 1.5	32 x 1.5	25
52104320LF	50 x 1.5	40 x 1.5	10
52104321LF	63 x 1.5	40 x 1.5	10
52104322LF	63 x 1.5	50 x 1.5	10
52006575LF	72 x 2	63 x 1.5	1
SKINDICHT® MR-M, blank brass			
52006579	80 x 2	75 x 1.5	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16