

SKINDICHT® JT PTFE metric

SKINDICHT® JT PTFE metric, sealing rings, suitable for foodstuffs, resistant to oil, water, alkaline solutions, acids, solvents etc



Food & Beverage



Good chemical resistance



Acid-resistant



Temperature-resistant

Benefits

Resistant to oil, water, alkaline solutions, acids, solvents, etc.
Suitable for foodstuffs

Application range

PTFE sealing disks for SKINTOP® and SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 Class-Description: Sealing ring

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class-Description: Sealing ring

Colour delivered:

White

Material:

PTFE

Temperature range:

-120 °C to +250 °C

Short-term: up to +300 °C

SKINDICHT® JT PTFE metric

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® JT PTFE metric

Article number	Article designation / size	Inner Ø (mm)	Thickness (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® JT PTFE metric					
53801030	M 12	12.1	2.0	16.6	100
53801040	M 16	16.1	2.0	21.1	100
53801050	M 20	20.1	2.0	27.5	100
53801060	M 25	25.1	3.0	33.4	50
53801070	M 32	32.1	3.0	40.3	50
53801080	M 40	40.2	3.0	51.5	25
53801090	M 50	50.2	3.0	61.6	25
53801100	M 63	63.2	3.0	73.9	25