

## SKINDICHT® SM-NPT

SKINTOP® SM-NPT, nickel-plated brass NPT threaded counter nut



Good chemical resistance



Mechanical resistance

### Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

### Product Make-up

NPT connection thread

### Note

Other sizes are available upon request

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® SM-NPT**

Article number	Article designation / size	Pieces / PU
52103540	NPT 1/2"	50
52103550	NPT 3/4"	20
52103560	NPT 1"	20
52103570	NPT 1 1/4"	20
52103580	NPT 1 1/2"	10
52103590	NPT 2"	10

Last Update (26.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16