

SKINTOP® GMP-GL NPT

SKINTOP® GMP-GL NPT



Assembly time



Temperature-resistant

Benefits

Glass fibre-reinforced for maximum mechanical stability

Application range

For locking SKINTOP® cable glands in boreholes without thread.

Product Make-up

NPT connection thread

Available without collar

(without surface for assembling tool)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Colour delivered:

Silver grey (RAL 7001)

Light grey (RAL 7035)

Black (RAL 9005)

Material:

Polyamide, glass fibre-reinforced

Temperature range:

-20 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® GMP-GL NPT

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® GMP-GL NPT

Article number	Article designation / size	Thickness (mm)	SW wrench size mm	Pieces / PU
SKINTOP® GMP-GL NPT silvergrey				
53019301	NPT 3/8"	5.0	22	100
53019311	NPT 1/2"	6.0	27	100
53019321	NPT 3/4"	7.0	36	100
53019331	NPT 1"	7.0	42	100
SKINTOP® GMP-GL NPT black				
53019305	NPT 3/8"	5.0	22	100
53019315	NPT 1/2"	6.0	27	100
53019325	NPT 3/4"	7.0	36	100
53019335	NPT 1"	7.0	42	100
SKINTOP® GMP-GL NPT lightgrey				
53019300	NPT 3/8"	5.0	22	100
53019310	NPT 1/2"	6.0	27	100
53019320	NPT 3/4"	7.0	36	100
53019330	NPT 1"	7.0	42	100

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16