

## SKINTOP® GMP-GL NPT

SKINTOP® GMP-GL NPT



Assembly time



Temperature-resistant

### Benefits

Glass fibre-reinforced for maximum mechanical stability

### Application range

For locking SKINTOP® cable glands in boreholes without thread.

### Product Make-up

NPT connection thread

Available without collar

(without surface for assembling tool)

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Colour delivered:

Silver grey (RAL 7001)

Light grey (RAL 7035)

Black (RAL 9005)

Material:

Polyamide, glass fibre-reinforced

Temperature range:

-20°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® GMP-GL NPT

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® GMP-GL NPT**

| Article number                 | Article designation / size | Thickness (mm) | SW wrench size mm | Pieces / PU |
|--------------------------------|----------------------------|----------------|-------------------|-------------|
| SKINTOP® GMP-GL NPT silvergrey |                            |                |                   |             |
| 53019301                       | NPT 3/8"                   | 5.0            | 22                | 100         |
| 53019311                       | NPT 1/2"                   | 6.0            | 27                | 100         |
| 53019321                       | NPT 3/4"                   | 7.0            | 36                | 100         |
| 53019331                       | NPT 1"                     | 7.0            | 42                | 100         |
| SKINTOP® GMP-GL NPT black      |                            |                |                   |             |
| 53019305                       | NPT 3/8"                   | 5.0            | 22                | 100         |
| 53019315                       | NPT 1/2"                   | 6.0            | 27                | 100         |
| 53019325                       | NPT 3/4"                   | 7.0            | 36                | 100         |
| 53019335                       | NPT 1"                     | 7.0            | 42                | 100         |
| SKINTOP® GMP-GL NPT lightgrey  |                            |                |                   |             |
| 53019300                       | NPT 3/8"                   | 5.0            | 22                | 100         |
| 53019310                       | NPT 1/2"                   | 6.0            | 27                | 100         |
| 53019320                       | NPT 3/4"                   | 7.0            | 36                | 100         |
| 53019330                       | NPT 1"                     | 7.0            | 42                | 100         |

Last Update (1.1.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16