

SKINDICHT® BL FKM

SKINDICHT® BL, brass blind plug with FKM o-ring and PG thread, assembly with screwdriver



-  Mechanical and plant engineering
-  Good chemical resistance
-  Mechanical resistance
-  Oil-resistant
-  Space requirement
-  Robust
-  Temperature-resistant
-  Waterproof

Product features

Assembling with screwdriver

Product Make-up

PG connection thread

Technical Data

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® BL FKM

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class-Description: Plug for cable screw gland
Material:	Body: nickel-plated brass O-Ring: FKM
Protection rating:	IP 66 IP 68 - 10 bar
Temperature range:	-20°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® BL FKM

Article number	Article designation / size	Thread length D mm	Pieces / PU
52003398	PG 7	5	50
52003399	PG 9	6	50
52003401	PG 11	6	50
52003402	PG 13,5	6.5	50
52003403	PG 16	6.5	50
52003404	PG 21	7	25
52003405	PG 29	8	25
52003406	PG 36	9	25
52003407	PG 42	10	5
52003408	PG 48	10	5

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16