

SKINDICHT® SM INOX

SKINDICHT® SM, counter nuts for thin walled-housings with through-holes, to counter a gland



Good chemical resistance



Mechanical resistance

Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

Product Make-up

PG connection thread

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class-Description: Locknut for cable screw gland

Material:

Stainless steel

Temperature range:

-60 °C to +200 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SM INOX

Article number	Article designation / size	Height (mm)	SW wrench size mm	Pieces / PU
52032517	PG 7	3.5	17	50
52032559	PG 11	3.5	22	50
5203254	PG 13,5	4.0	24	50
52032555	PG 16	4.0	27	50
52032556	PG 21	4.5	32	25
52032557	PG 29	5.5	41	10
52032558	PG 36	6.0	51	10

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16