

SKINDICHT® ZS-M

SKINDICHT® ZS-M, hexagonal converter from a metric outer thread to a PG inner thread, assembling with a wrench



Robust

Benefits

Enables the use of PG accessories in metric threads
Assembling with a wrench

Application range

Hexagonal converter from a metric outer thread to a PG inner thread.
Machines
Devices
Housings

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Note

SKINDICHT® ZS-M-XL offers a long metric connection thread

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441
ETIM 6.0 Class-Description: Cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60°C to +200°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® ZS-M

Article number	Thread, male M1	Pieces / PU
SKINDICHT® ZS-M		
52104330	12 x 1.5	100
52104340	16 x 1.5	100
52104010	16 x 1.5	100
52104360	20 x 1.5	100
52104370	20 x 1.5	100
52104380	20 x 1.5	50
52104400	25 x 1.5	50
52104410	32 x 1.5	25
52104420	40 x 1.5	10
52104430	50 x 1.5	10
52104440	63 x 1.5	10
SKINDICHT® ZS-M-XL		
52104335	12 x 1.5	100
52104345	16 x 1.5	100
52104365	20 x 1.5	100
52104375	20 x 1.5	100
52104385	20 x 1.5	50
52104405	25 x 1.5	50
52104415	32 x 1.5	25
52104425	40 x 1.5	10
52104435	50 x 1.5	10
52104445	63 x 1.5	10

Last Update (16.09.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16