

SKINDICHT® SHV cone seal

SKINDICHT® SHV cone seal



Good chemical resistance



Acid-resistant



Temperature-resistant

Benefits

SKINDICHT® SHV CR resistant to oil, dust and water

SKINDICHT® SHV FKM for high temperatures

SKINDICHT® SHV FKM resistant to oils, solvents, acids and chemicals

Application range

Sealing cone for SKINDICHT® cable glands.

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000451

ETIM 5.0 Class-Description: Cable plug sealing clamp

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000451

ETIM 6.0 Class-Description: Cable plug sealing clamp

Colour delivered:

CR: black

FKM: red

Material:

CR

FKM

Temperature range:

CR: -20°C to +80°C

FKM: -20°C to +200°C

Note

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SHV cone seal

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SHV cone seal

Article number	PG size/clear opening	Inner Ø (mm)	Length (mm)	Pieces / PU
SKINDICHT® SHV CR				
52021120	SHV 7/ 5.0	5.0	13.8	100
52021130	SHV 9/ 6.0	6.0	14.8	100
52021140	SHV 9/ 7.0	7.0	14.8	100
52021150	SHV 11/ 7.0	7.0	17.5	100
52021160	SHV 11/ 9.0	9.0	17.0	100
52021180	SHV13.5/ 9.0	9.0	18.5	100
52021170	SHV13.5/ 11.0	11.0	18.5	100
52021190	SHV 16/ 11.0	11.0	19.5	50
52021200	SHV 16/ 13.0	13.0	19.5	50
52021210	SHV 16/ 15.0	15.0	19.5	50
52024460	SHV 21/ 16.0	16.0	19.8	50
52021220	SHV 21/ 18.0	18.0	19.8	50
52021230	SHV 21/ 20.0	20.0	19.8	50
52021240	SHV 29/ 22.0	22.0	24.0	25
52021250	SHV 29/ 24.0	24.0	24.0	25
52021260	SHV 29/ 26.0	26.0	24.0	25
SKINDICHT® SHV FKM				
52021259	SHV 7/ 5.0	5.0	13.8	100
52021146	SHV 9/ 6.0	6.0	14.8	100
52021261	SHV 9/ 7.0	7.0	14.8	100
52021262	SHV 11/ 7.0	7.0	17.5	100
52021263	SHV 11/ 9.0	9.0	17.0	100
52021271	SHV 13.5/ 9.0	9.0	18.5	100
52021272	SHV 13.5/ 11.0	11.0	18.5	100
52021265	SHV 16/ 13.0	13.0	19.5	50
52021269	SHV 16/ 15.0	15.0	19.5	50
52021268	SHV 21/ 18.0	18.0	19.5	50
52021266	SHV 21/ 20.0	20.0	19.8	50
52021267	SHV 29/ 22.0	22.0	19.8	50

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16