

SKINMATIC® RZ

SKINMATIC® RZ, universal mounting tool, adjustable for all wrench sizes ranging from 14-33mm, assembling after the cables are already inserted



Assembly time



Space requirement

Benefits

Adjustable for all wrench sizes ranging from 14 to 33 mm

Assembling after the cables are already inserted

Ergonomic plastic grips

Application range

For quick allocation of cable and conduit glands

Product features

Made of chromium-plated tool steel

With two expandable clamping ranges (lock positions)

Small opening (14 - 22 mm): M12 to M16, PG7 to PG11, NPT 3/8"

Large opening (24 - 33 mm): M20 to M25, PG13.5 to PG21, NPT 1/2" to 3/4"

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002498

ETIM 5.0 Class-Description: Accessories for low-voltage switch technology

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002498

ETIM 6.0 Class-Description: Accessories for low-voltage switch technology

Note

Not subjected to RoHS directive.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINMATIC® RZ

Article number	Article designation / size	Width of flat surface (mm)	Overall length C mm	Pieces / PU
SKINMATIC® RZ				
61791260	SKINMATIC® RZ	14 - 33	250.0	1

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16