

SKINTOP® BRUSH ADD-ON 24

SKINTOP® BRUSH ADD-ON 24, EMC Kit with brush technology suitable for the SKINTOP® multi cable bushing systems for the 24 pin cut-outs

Info

EMC Kit with brush technology suitable for the SKINTOP® multi cable bushing systems for the 24 pin cut-outs



Reliability



Voltage



Interference signals



Temperature-resistant

Benefits

- Faster, easier screen contact
- Optimum EMC protection
- Quicker installation and EMC contacting compared with other systems
- Maximum assembly freedom during adjustment
- Usable with different cable diameters at the same time

Application range

- For the EMC screen contacting of cables when using the SKINTOP® multi-cable entry systems
- For EMC-compliant earthing of the copper braiding
- Control cabinet manufacturing
- Automation systems

Product features

- Low-resistance screen contact

Last Update (02.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® BRUSH ADD-ON 24

Visible, large-scale screen contact

Included

Brush frame
Spacers
Mounting material

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000240 ETIM 5.0 Class-Description: Cable entry system
Material:	Frame: Aluminium EMC brush: brass
Temperature range:	-30°C to +110°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® BRUSH ADD-ON 24

Article number	Dimensions overall	Executions range	Borehole	Pieces / PU
52220089	40x120 mm	47.0 - 120.0	4.2	1

Last Update (02.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16