

SKINTOP® SDVR-M ATEX

SKINTOP® SDV-M ATEX Dust protection



Assembly time



Reliability

Benefits

Permanent and secure sealing for areas with risks of explosion
Easy to assemble
High degree of protection

Application range

SKINTOP® SDVR-M is used together with SKINTOP® MSR-M ATEX or SKINTOP® KR-M ATEX plus (blue)
Equipment group II / Category 2G+1D

Note

Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® STR-M and SKINTOP® MSR-M

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 Class-Description: Plug for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class-Description: Plug for cable screw gland

Caution:

Refer to the instruction leaflet for the installation dimensions and torques

Material:

CR

Protection rating:

IP 68 - 10 bar

Temperature range:

-30°C to +70°C

Short-term: up to +90°C

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® SDVR-M ATEX

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SKINTOP® SDVR-M ATEX

Article number	Article designation / size	Visible height (mm)	PU
SKINTOP® SDVR-M ATEX			
541 13013	M 16 ATEX	4.0	50
541 13023	M 20 ATEX	5.0	50
541 13033	M 25 ATEX	5.0	50
541 13043	M 32 ATEX	5.5	25

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16