



SKINTOP® INOX NPT

SKINTOP® INOX / SKINTOP® INOX-R, corrosion-resistant stainless steel cable gland with smooth surfaces, compact design, sea water-resistant

Info

Stainless steel version with compact design

For use in the splash zone in the food production



Food & Beverage



Suitable for outdoor use



Good chemical resistance



Wide clamping range



Halogen-free



Mechanical resistance



Temperature-resistant

Benefits

Corrosion-resistant

Sea water-resistant

Smooth surfaces - no edges

Compact design

Wide, variable clamping ranges

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® INOX NPT

Application range

Onshore and offshore applications
Bottling plants and breweries
Food industry (product-free zone, splash zone)

Norm references / Approvals

ECOLAB®
Industry standard in the field of professional cleaning and disinfection in the food and beverage industry
DIN EN 1672-2
Guideline for the design of machinery
DIN EN ISO 14159
Security of machinery – Hygienic requirements for the design of machinery
NSF/ANSI 169
Hygienic design for machinery and components

Product Make-up

NPT connection thread acc. to ASME B1.20.1 - 2013

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Material:	Body: stainless steel V4A (1.4404 / 316L) Insert: polyamide Sealing: silicone O-Ring: silicone Halogen-free
Protection rating:	IP 68 - 5 bar IP 69 NEMA Type 1, 2, 4x, 6, 12
Temperature range:	-40°C to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINTOP® INOX NPT

Article number	Article designation / size	Ø F mm	SW wrench size mm	Overall length C mm	Thread length D mm	Pieces / PU
SKINTOP® INOX NPT						
53806778	NPT 1/4"	4 - 7	16	37.8	15	5
53806779	NPT 3/8"	6 - 10	20	40.4	15	5
53806780	NPT 1/2"	7 - 13	24	42.5	15	5
53806781	NPT 3/4"	9 - 17	29	46.2	15	5
53806782	NPT 1"	11 - 21	36	50.6	15	5
53806783	NPT 1 1/4"	19 - 28	45	59.2	17	5
53806784	NPT 1 1/2"	27 - 35	54	63.2	17	5
SKINTOP® INOX-R NPT						
53806796	NPT 1/4"	3 - 5	16	37.8	15	5
53806797	NPT 3/8"	5 - 7	20	40.4	15	5
53806798	NPT 1/2"	6 - 10	24	42.5	15	5
53806799	NPT 3/4"	7 - 13	29	46.2	15	5
53806800	NPT 1"	8 - 15	36	50.6	15	5
53806801	NPT 1 1/4"	15 - 23	45	59.2	17	5
53806802	NPT 1 1/2"	22 - 29	54	63.2	17	5