

## Connector RJ45 CAT.5 Stewart SS37

RJ45 field mountable connector, qualified for 100Mbit - data transmission  
suitable for industrial environment and Officearea  
Stewart SS37



### Product features

Screened version  
Suitable for stranded conductors (AWG26)  
Included: bend protection and guide plate  
Anti-kink protection: light grey  
Max. outer sheath diameter: 5.72 mm

### Technical Data

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

### Note

Stewart is a registered trademark of Bel Fuse Inc.

Other colours are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**Connector RJ45 CAT.5 Stewart SS37**

Article number	Article designation
CE6323	Connector RJ45 CAT.5 Stewart SS37

Last Update (18.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16