

EPIC® SENSOR M12A Screw termination

Field mountable connectors M12

Off into the field: be it in the F&B, mechanical engineering or intralogistics areas, the M12A data connector is an expert in the field of signal transmission at sensor-actuator level. With this plastic connector, cable assembly can be carried out without any special tools whatsoever thanks to the screw connection. Numerous variants are available.



Supplementary automation components from Lapp



Mechanical and plant engineering



Assembly time



Waterproof

Benefits

High stability thanks to impact-resistant polyamide.

The service-friendly screw connection makes assembly possible without a special tool, and is suitable for connections which need to be detached again.

When connected, protection class IP 67 can be achieved.

Available in different designs and with different pole configurations.

Application range

Can be used universally at machine interfaces for many applications in data and signal transmission in the low-frequency range.

Typical application areas are sensors and actuators at field level.

Good oil and chemical resistance.

Product features

4, 5 and 8-pin version

Screened and non-screened version

Screw connection or insulation displacement contacts (IDC)

PWIS-free

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002062

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SENSOR M12A Screw termination

Classification ETIM 6:	ETIM 5.0 Class-Description: Sensor-actuator connector ETIM 6.0 Class-ID: EC002062 ETIM 6.0 Class-Description: Sensor-actuator connector
Material:	Contact: CuZn Contact surface: CuSnZn
Protection rating:	IP 67
Ambient temperature (operation):	-25°C to +85°C
Contact material:	Copper alloy
Contact surface material:	Au (gold)
Coding:	A-standard

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SENSOR M12A Screw termination

Article number	Number of pins	Connection type	PL_DYN_LEITERQUERSCHNITTF LEXIBEL_MM	PL_DYN_DURCHMESSER_EPIC
381166325	3	Socket	1.5	4.0 - 8.0
381166326	4	Socket	1.5	4.0 - 8.0
381166327	5	Socket	1.5	4.0 - 8.0
381166328	8	Socket	1.0	4.0 - 8.0
381166338	3	angled	1.5	4.0 - 8.0
381166339	4	angled	1.5	4.0 - 8.0
381166341	5	angled	1.5	4.0 - 8.0
381166343	8	angled	1.0	4.0 - 8.0
381166332	3	-	1.5	4.0 - 8.0
381166333	4	-	1.5	4.0 - 8.0
381166335	5	-	1.5	4.0 - 8.0
381166337	8	-	1.0	4.0 - 8.0
381166318	3	-	1.5	4.0 - 8.0
381166319	4	-	1.5	4.0 - 8.0
381166320	5	-	1.5	4.0 - 8.0
381166321	8	-	1.0	4.0 - 8.0

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

EPIC® SENSOR M12A Screw termination



Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16