

## UNITRONIC® SENSOR Valve-M12

valve connector on straight M12 plug

Sensor/actuator cordset, Valve connector on M12 plug, PUR halogenfree, 3-pin, with LED, Typ A, Typ B, Typ C, IP65/IP67



Supplementary automation components from Lapp



Mechanical and plant engineering



Assembly time



Space requirement



Power chain



Waterproof

### Benefits

Cost-saving due to quick and easy installation

Space-saving due to compact dimensions.

Fast and easy error tracking

### Product features

Suitable for drag chains

With protective circuit (Z diode), PE-bridged (except type AD)

With LED status indicator (yellow)

With display switch state (2 LEDs, red/green)

Including tag carrier

PWIS-free

### Product Make-up

3 or 5 x 0.5 mm<sup>2</sup>

Core identification code:

Black cores with white numbers +green/yellow

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® SENSOR Valve-M12

Outer sheath: PUR halogen-free, black  
Outer diameter:  
4.5 mm (3 pins)  
5.3 mm (5 pins)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001855 ETIM 5.0 Class-Description: Sensor-actuator patch cord
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001855 ETIM 6.0 Class-Description: Sensor-actuator patch cord
Material:	Contact: CuSn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing
Protection rating:	IP65/IP67
Ambient temperature (operation):	Valve connector -20 °C to +85 °C Connector/socket -25 °C to +90 °C Fixed installation -40 °C to +80 °C Flexing -20 °C to +80 °C
Coding:	A-standard
Rated current (A):	4 A

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: inclusive of copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**UNITRONIC® SENSOR Valve-M12**

Article number	Article designation	Number of pins	Length (m)	LED	Rated voltage (V)	PU
Straight connector to valve connector type A (18 mm)						
22260550	AB-C3-M12MS-0,3PUR-A-1L-S	3	0.3	1 LED	24	1
22260551	AB-C3-M12MS-0,6PUR-A-1L-S	3	0.6	1 LED	24	1
22260552	AB-C3-M12MS-1,0PUR-A-1L-S	3	1	1 LED	24	1
22260553	AB-C3-M12MS-2,0PUR-A-1L-S	3	2	1 LED	24	1
Straight connector to valve connector type A (18mm) for pressure switch						
22260573	AB-C5-M12MS-0,3PUR-AD-2L	5	0.3	2 LEDs	24	1
22260572	AB-C5-M12MS-0,6PUR-AD-2L	5	0.6	2 LEDs	24	1
22260571	AB-C5-M12MS-1,0PUR-AD-2L	5	1	2 LEDs	24	1
22260570	AB-C5-M12MS-2,0PUR-AD-2L	5	2	2 LEDs	24	1
Straight connector to valve connector type B (10 mm)						
22260558	AB-C3-M12MS-0,3PUR-B-1L-S	3	0.3	1 LED	24	1
22260559	AB-C3-M12MS-0,6PUR-B-1L-S	3	0.6	1 LED	24	1
22260560	AB-C3-M12MS-1,0PUR-B-1L-S	3	1	1 LED	24	1
22260561	AB-C3-M12MS-2,0PUR-B-1L-S	3	2	1 LED	24	1
Straight connector to valve connector type BI (11 mm)						
22260554	AB-C3-M12MS-0,3PUR-BI-1L-S	3	0.3	1 LED	24	1
22260555	AB-C3-M12MS-0,6PUR-BI-1L-S	3	0.6	1 LED	24	1
22260556	AB-C3-M12MS-1,0PUR-BI-1L-S	3	1	1 LED	24	1
22260557	AB-C3-M12MS-2,0PUR-BI-1L-S	3	2	1 LED	24	1
Straight connector to valve connector type C (8 mm)						
22260566	AB-C3-M12MS-0,3PUR-C-1L-S	3	0.3	1 LED	24	1
22260567	AB-C3-M12MS-0,6PUR-	3	0.6	1 LED	24	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**UNITRONIC® SENSOR Valve-M12**

Article number	Article designation	Number of pins	Length (m)	LED	Rated voltage (V)	PU
	C-1L-S					
22260568	AB-C3-M12MS-1,0PUR-C-1L-S	3	1	1 LED	24	1
22260569	AB-C3-M12MS-2,0PUR-C-1L-S	3	2	1 LED	24	1
Straight connector to valve connector type CI (9.4 mm)						
22260562	AB-C3-M12MS-0,3PUR-CI-1L-S	3	0.3	1 LED	24	1
22260563	AB-C3-M12MS-0,6PUR-CI-1L-S	3	0.6	1 LED	24	1
22260564	AB-C3-M12MS-1,0PUR-CI-1L-S	3	1	1 LED	24	1
22260565	AB-C3-M12MS-2,0PUR-CI-1L-S	3	2	1 LED	24	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16