

EPIC® M23P Socket contacts

Contacts, tools, accessories for circular connectors

EPIC® M23P Socket contacts

Info

All contacts are high quality gold plated

Contacts are designed for wide crimping range, therefore low number of variants

Made in Germany



Good chemical resistance



Wide clamping range



Corrosion-resistant



Maximum vibration protection



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust



Reliability

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (01.02.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® M23P Socket contacts

Article number	Article designation	Description	For design	Pieces / PU
381167757	EPIC M23P CONTACT SOCKET 1MM 0.14-1	Female contacts	for type D6	100
381167758	EPIC M23P CONTACT SOCKET 1MM 0.5-1.5	Female contacts	for type D6	100
381167755	EPIC M23P CONTACT SOCKET 2MM 0.35-2.5	Female contacts	for type D6	100
381167756	EPIC M23P CONTACT SOCKET 2MM 2.5-4	Female contacts	for type D6	100

Last Update (01.02.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

EPIC® M23P Socket contacts



EPIC® M23P Socket contacts

