

EPIC® POWER M12S Screw termination

Circular connectors for servomotors and power supply

This compact M12 connector with PE contact comes into play if you want more power. It is used to supply power to three-phase motors (630 V, 12 A per contact). The S-coding prevents incorrect plugging with other connectors.



Low weight



Space requirement



Waterproof

Benefits

High stability thanks to impact-resistant polyamide.

Powerful up to 12 A despite extremely space-saving size for the tightest of spaces.

The mechanical S-coding of the connector face prevents incorrect plugging with mating connectors.

The service-friendly screw connection makes assembly possible without a special tool, and is suitable for connections which need to be detached again.

Available in different designs and with different pole configurations.

Application range

For connecting three-phase motors with up to 7.5 kW.

For power supply connection of devices and machines in various applications.

Good oil and chemical resistance.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002635

ETIM 5.0 Class-Description: Circular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002635

ETIM 6.0 Class-Description: Circular connector (industrial connector)

Rated voltage (V):

630 V

Rated impulse voltage:

6 kV

Rated current (A):

12 A

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® POWER M12S Screw termination

Pollution degree:	3
Number of contacts:	3 + PE S-coded
Termination methods:	Screw termination: 0.5 - 2.5 mm ²
Protection rating:	IP 67
Cycle of mechanical operation:	100
Temperature range:	-25°C ... +85°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® POWER M12S Screw termination

Article number	Article description	Version	Version	Contacts included	Clamping range min	Clamping range max	Fastening type
381166306	Straight female	Socket	female	4	8	12	M12
381166307	Angled socket	Socket	female	4	8	12	M12
381166309	Straight male	plug	male	4	8	12	M12
381166310	Angled male	plug	male	4	8	12	M12

EPIC® POWER M12S Screw termination

