

## EPIC® POWERLOCK Screw contacts

Contacts, tools, accessories for circular connectors

EPIC® POWERLOCK 400A screw contacts from 50mm<sup>2</sup> up to 120mm<sup>2</sup>

### Info

Screw max. 400 A

Do not plug with crimp-type (660 A)

Made in Europe



### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® POWERLOCK Screw contacts**

Article number	Article designation	Version	For design	PU
44420241	POWERLOCK SP M12	Contact Drain, M12 Thread for cable lugs	for type A1	1
Source - for type A6 S				
44420242	POWERLOCK QP M12	Lamella contact source, M12 thread for cable lug	for type A6	1
44420232	POWERLOCK SS 120	120 mm <sup>2</sup>	for type F6	1
Source - for type D6 S				
44420237	POWERLOCK QS 120	120 mm <sup>2</sup>	for type D6	1

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16

## EPIC® POWERLOCK Screw contacts

