

## POWERLOCK BOX S\*

Circular connectors for servomotors and power supply

POWERLOCK BOX 400A version for 19 Zoll slot

### Info

Can be locked to prevent unauthorised disconnection

Made in Europe



Wide clamping range



Optimum strain relief



Robust



Reliability



Waterproof

### Benefits

Guarantees the correct sequence is followed when connecting and disconnecting a set of connectors (PE, N, L1, L2, L3)

Every colour has a different coding to prevent incorrect plugging

IP 20 finger-protected

Integrated micro-switch that can be connected to circuit breaker or alarm circuit

### Application range

Alternative energy installations

For mobile and stationary power distribution

For the connection of motors, transformers and generators

Light & sound technology

Last Update (12.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## POWERLOCK BOX S\*

### Product features

Included: Contacts with M12 threaded post  
Cable connector for microswitch optional  
19" housing with height unit 2HE/2U

### Housings

Sealed security lid is optional

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002635 ETIM 5.0 Class-Description: Circular connector (industrial connector)
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002635 ETIM 6.0 Class-Description: Circular connector (industrial connector)
Rated voltage (V):	1000 V
Rated current (A):	Screw max. 400 A
Pollution degree:	3
Contacts:	Screw termination: silver-plated brass
Number of contacts:	4 + PE
Termination methods:	Screw termination: 50 - 120 mm <sup>2</sup>
Protection rating:	IP 65 (latched)
Cycle of mechanical operation:	500
Temperature range:	-20 °C ... +85 °C

### Note

\* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**POWERLOCK BOX S\***

Article number	Article description	Fastening type	Pin configuration	Packaging unit
44420282	POWERLOCK BOX A1 S	Ø 6.5 mm (4x)	4+PE	1
Type A1, drain, with cover				
44420283	POWERLOCK BOX A1 SD	Ø 6.5 mm (4x)	4+PE	1
Type A6, source				
44420286	POWERLOCK BOX A6 S	Ø 6.5 mm (4x)	4+PE	1
Type A6, source, with cover				
44420287	POWERLOCK BOX A6 SD	Ø 6.5 mm (4x)	4+PE	1

Last Update (12.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

## POWERLOCK BOX S\*

