
# EPIC® H-D 1.6 stamped contacts

For inserts and modules of the EPIC® rectangular connectors

With H-D 1.6 pressed contacts, handling is easy using the removal tool, crimping pliers and locator.

## Info

Choice of high quality gold or silver plated contacts
Two crimp areas with wire and insulation crimp



## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000796<br>ETIM 5.0 Class-Description: Contact for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000796<br>ETIM 6.0 Class-Description: Contact for industrial connectors |

## Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.


©2025 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

# EPIC® H-D 1.6 stamped contacts

| Article number | Article description | Contact type | Conductor cross-section ($mm^2$) | Surface | Stripping length (mm) | Packaging unit |
|---|---|---|---|---|---|---|
| Contacts | | | | | | |
| 11241100 | H-D 1.6 stamped | male | 0.14 - 0.5 | Ag | 3,0 | 100 |
| 11231100 | H-D 1.6 stamped | female | 0.14 - 0.5 | Ag | 3,0 | 100 |
| 11221000 | H-D 1.6 stamped | male | 0.5 - 1.5 | Ag | 4,0 | 100 |
| 11236100 | H-D 1.6 stamped | female | 0.5 - 1.5 | Ag | 4,0 | 100 |
| 11223500 | H-D 1.6 stamped | male | 1.5 - 2.5 | Ag | 4,0 | 100 |
| 11228500 | H-D 1.6 stamped | female | 1.5 - 2.5 | Ag | 4,0 | 100 |
| 11243100 | H-D 1.6 stamped | male | 0.14 - 0.5 | Au | 3,0 | 100 |
| 11233100 | H-D 1.6 stamped | female | 0.14 - 0.5 | Au | 3,0 | 100 |
| 11221300 | H-D 1.6 stamped | male | 0.5 - 1.5 | Au | 4,0 | 100 |
| 11238100 | H-D 1.6 stamped | female | 0.5 - 1.5 | Au | 4,0 | 100 |

Last Update (05.04.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16