

EPIC® SIGNAL D-SUB Contacts

EPIC® SIGNAL DSUB contacts for M23 DSUB inserts, MC 20 module, MH Gigabit module

Info

Made in Germany



Supplementary automation components from Lapp



Mechanical and plant engineering



Rail



Wind Energy



Suitable for outdoor use



Robust



Voltage

Technical Data

Termination methods:

Crimp termination: 0,25mm² ... 1,0mm²

Material:

brass gold plated CuZn / Au

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (23.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® SIGNAL D-SUB Contacts

Article number	Article description	Version	Version	Contact type	Conductor cross-section AWG	Surface	Stripping length (mm)	Pieces / PU
44423357	D-SUB 1,0 machined	wklad M23 D-Sub	1mm male crimp 0.25-1.0mm ²	male	0.25 - 1.0	Au	6,0	100
44423356	D-SUB 1,0 machined	wklad M23 D-Sub	1mm female crimp 0.25-1.0mm ²	female	0.25 - 1.0	Au	6,0	100

Last Update (23.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16