

## MC 6.0 machined contacts

For inserts and modules of the EPIC® rectangular connectors

The modular machined contacts 6.0 are to be used together with the pneumatic crimping tool, Klauke type EK 60/22-L.

### Info

silver plated and passivated contacts



### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Contact resistance:

< 1 mOhm

Material:

Copper alloy, hard silver-plated

Cycle of mechanical operation:

500

### Note

\* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**MC 6.0 machined contacts**

Article number	Article description	Inserts	Version	Cross-section (mm <sup>2</sup> )	Cross-section identification	Surface	Pieces / PU
Contacts							
44424019	MC SCEM AG 16 D=6.0	Crimping contacts for HHC2 modules	male	16	1	Ag	20
44424022	MC BCEM AG 16 D=6.0	Crimping contacts for HHC2 modules	female	16	1	Ag	20
44424020	MC SCEM AG 25 D=6.0	Crimping contacts for HHC2 modules	male	25	2	Ag	20
44424023	MC BCEM AG 25 D=6.0	Crimping contacts for HHC2 modules	female	25	2	Ag	20
44424021	MC SCEM AG 35 D=6.0	Crimping contacts for HHC2 modules	male	35	3	Ag	20
44424024	MC BCEM AG 35 D=6.0	Crimping contacts for HHC2 modules	female	35	3	Ag	20
Crimping die for contacts of HHC2 modules							
44424025	TOOL DIE D=6.0/16 mm <sup>2</sup>	Crimping dies	-	16	-	-	1
44424026	TOOL DIE D=6.0/25 mm <sup>2</sup>	Crimping dies	-	25	-	-	1
44424027	TOOL DIE D=6.0/35 mm <sup>2</sup>	Crimping dies	-	35	-	-	1

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16

**MC 6.0 machined contacts**