

EPIC® H-B 24 TBF-LB

Housing design H-B. The industry standard.

The universal metal housing with a single lever and a direct cable entry is ideal for investment construction applications.

Info

Single Lever version for quick locking and simple unlocking with lifting aid

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Safe fixing with 4 screws

Casted neck for easy assembly of the cable gland

Application range

Plant engineering

Light & sound technology

Plastics industry

Product features

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 TBF-LB

Cable coupler hood, low version
Single lever
Straight cable entry
Versions with / without neck

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR |
| Protection rating: | IP 65 (latched) NEMA 250, UL50E: 12 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40°C to +100°C, short-term up to +125°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 TBF-LB

| Article number | Article description | M | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: cable coupler hood (1 straight cable entry, single lever) | | | | | |
| 10127900 | H-B 24 TBF-LB 21 | - | 21 | yes | 5 |
| 10117900 | H-B 24 TBF-LB 29 | - | 29 | yes | 5 |
| 19127900 | H-B 24 TBF-LB M25 | 25 | - | - | 5 |
| 19117900 | H-B 24 TBF-LB M32 | 32 | - | - | 5 |