

EPIC® H-B 24 TG

Housing design H-B. The industry standard.

The robust housing for rectangular connectors is suitable for investment construction and consists of a hood, pivots for a double lever and a direct cable entry.

Info

Non-slip ridges for comfortable disconnecting

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Ideal for many applications due to a wide range of housings and inserts

M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering

Light & sound technology

Plastics industry

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 TG

Product features

Hood, low version
Bolts for double lever
Straight cable entry
Versions with / without neck

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR |
| Protection rating: | IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 TG

| Article number | Article description | M | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: hood (straight cable entry, bolts for double lever) | | | | | |
| 10121000 | H-B 24 TG 21 | - | 21 | yes | 5 |
| 10111000 | H-B 24 TG 29 | - | 29 | yes | 5 |
| 19121000 | H-B 24 TG M25 | 25 | - | - | 5 |
| 19111000 | H-B 24 TG M32 | 32 | - | - | 5 |
| 19111500 | H-B 24 TG M40 | 40 | - | - | 5 |