

EPIC® H-B 24 TSH

Housing design H-B. The industry standard.

The metal housing for rectangular connectors is ideal for use in investment construction. It has a side cable entry and pivots for a double lever.

Info

- Non-slip ridges for comfortable disconnecting
- More interior space for wiring
- Protection rating UL50E tested



- Supplementary automation components from Lapp
- Mechanical and plant engineering
- Mechanical resistance
- Robust
- Waterproof

Benefits

Ideal for many applications due to a wide range of housings and inserts
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (16.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 TSH

Product features

Hood, high version
Bolts for double lever
Side cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 TSH

Article number	Article description	M	PG	Neck	Packaging unit
H-B housing: hood (side cable entry, bolts for double lever, high version)					
70152400	H-B 24 TSH 21	-	21	yes	5
70152600	H-B 24 TSH 29	-	29	yes	5
79152400	H-B 24 TSH M25	25	-	-	5
79152600	H-B 24 TSH M32	32	-	-	5
79152800	H-B 24 TSH M40	40	-	-	5

Last Update (16.07.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16